

Test Report



| Sample Information | |
|--------------------|---------------------------|
| Item Description: | Hook & Eye/Sleek SoftSeal |
| Colour: | Basic White |
| Test Methods: | ISO & AATCC |

| Test Method | Requirement | Conformity |
|--|---|------------|
| » COLORFASTNESS TO LAUNDERING: ACCELERATED (AATCC 61 2A) | Colour Change : 4.0 Colour Stain : 3.5 | Pass |
| » COLOURFASTNESS TO PERSPIRATION (ISO 105-E04) | Colour Change : 4.0 Colour Stain : 3.5 | Pass |
| » COLOURFASTNESS TO WATER (ISO 105 E01) | Colour Change : 4.0 Colour Stain : 3.5 | Pass |
| » RESISTANCE TO PHENOLIC YELLOWING (ISO105-X18) | Colour Change : 4.0 | Pass |
| » APPEARANCE AFTER REPEATED LAUNDERING | Visual rating - evaluation after 1x, 5x washed | Pass |
| » DIMENSIONAL CHANGE AFTER HOME LAUNDERING (AATCC 135 / AATCC 150) | Evaluation after 1x, 5x washed | Pass |
| » FREE NICKEL CONTENT(QUALITATIVE) | | Pass |
| » HOOK & EYE PULL OUT STRENGHT (ASTM D1683 MOD) | 20 lbs. Minimum | Pass |
| » HOOK TO EYE ATTACHMENT STRENGTH | 1 Hook & Eye - 20 lb. min 2 & 3 Hook & Eyes - 30 lb. min | Pass |
| » MANUFACTURING QUALITY (VISUAL) | No sharp points or edges | Pass |



Samples for testing has been selected according to the Random Sampling Technique where each sample has an equal probability of being chosen. There is a possibility that the sample does not represent the population as a whole due to any random variation (Sampling Error). All tests are performed only by certified laboratory technicians.