

# Test Report



Sample Information	
Item Description:	Hook & Eye/SoftSeal
Colour:	Basic White
Test Methods:	ISO & AATCC

Test Method	Requirement	Conformity
»» COLORFASTNESS TO LAUNDERING: ACCELERATED (AATCC 61 2A)	Colour Change : 4.0 Colour Stain : 3.5	Pass
»» COLOURFASTNESS TO PERSPIRATION (ISO 105-E04)	Colour Change : 4.0 Colour Stain : 3.5	Pass
»» COLOURFASTNESS TO WATER (ISO 105 E01)	Colour Change : 4.0 Colour Stain : 3.5	Pass
»» RESISTANCE TO PHENOLIC YELLOWING (ISO105-X18)	Colour Change : 4.0	Pass
»» APPEARANCE AFTER REPEATED LAUNDERING	Visual rating - evaluation after 1x, 5x washed	Pass
»» DIMENSIONAL CHANGE AFTER HOME LAUNDERING (AATCC 135 / AATCC 150)	Evaluation after 1x, 5x washed	Pass
»» FREE NICKEL CONTENT(QUALITATIVE)		Pass
»» HOOK & EYE PULL OUT STRENGHT (ASTM D1683 MOD)	20 lbs. Minimum	Pass
»» HOOK TO EYE ATTACHMENT STRENGTH	1 Hook & Eye - 20 lb. min 2 & 3 Hook & Eyes - 30 lb. min	Pass
»» MANUFACTURING QUALITY (VISUAL)	No sharp points or edges	Pass



Samples for testing has been selected according to the Random Sampling Technique where each sample has an equal probability of being chosen. There is a possibility that the sample does not represent the population as a whole due to any random variation (Sampling Error). All tests are performed only by certified laboratory technicians.